

# Contec® Hands Free Mop Saturation System

Designed to simplify the cleanroom mopping process, Contec's Hands Free Mop Head Saturation System allows mop heads to be presaturated prior to being passed into the controlled environment. The system allows mop heads to be installed AND removed "hands-free" reducing the risk of cross contamination and speeding up the cleaning and disinfection process.

There is a choice of a system, with either two 15L polypropylene buckets or two 10L stainless steel buckets. A stainless steel cart holds the buckets, 2 easy-fit mop applicator frames, a diffuser tray, and the hands-free mop head removal system. The utility handle allows two small buckets (6L) to be positioned on the handle providing additional storage for extra supplies such as clean mop heads, spray bottles, wipes, and other items as needed.

A convenient clip and holder for the mop frame and handle when it is not in use, are also fixed to either side of the cart.

Being lightweight and manoueverable the trolley is very easy to use. The trolley is fitted with four autoclavable castors, meaning the whole trolley can be autoclaved before use. Each bucket is designed to allow 10 flat mop heads to be presaturated before being taken into the cleanroom. Or, the second bucket can be used for the dilution of a concentrate and to store the diffuser tray when not in use.

The mop heads are placed on the easy-fit mop applicator frame which coupled with the mop head design, means the mop heads can be fitted to the mop frame *hands-free*. A stainless steel disinfectant diffuser tray helps to evenly saturate every mop head. Once used the mop heads can also be removed *hands-free* using the unique mop removal system, straight into a waste bag if required.



polypropylene buckets (2041020)

| FEATURES                                                        | BENEFITS                                                                                                                                                                                               |
|-----------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Hands-free mop head application and removal</b>              | <ul style="list-style-type: none"><li>• Easy and convenient to use - used mops can be easily disposed of</li><li>• Reduces risk of cross contamination as dirty mops dont need to be handled</li></ul> |
| <b>Stainless steel diffuser and "A" frame</b>                   | <ul style="list-style-type: none"><li>• Allow mops to be presaturated prior to being passed into the cleanroom</li></ul>                                                                               |
| <b>Utility handle 1.04m high</b>                                | <ul style="list-style-type: none"><li>• Comfortable height allows for ease of use</li></ul>                                                                                                            |
| <b>Utility handle basket holds two 6L buckets</b>               | <ul style="list-style-type: none"><li>• Additional storage for clean mop heads, solution bottles, wipes, and other cleaning supplies if needed</li></ul>                                               |
| <b>Four rotating, lockable castors</b>                          | <ul style="list-style-type: none"><li>• Allows excellent manoeuvrability ideal for small cleanrooms and tight spaces</li><li>• Trolley position can be secured during cleaning tasks</li></ul>         |
| <b>On cart storage for two mop handles and frames</b>           | <ul style="list-style-type: none"><li>• Allows convenient storage of two mop handles and frames</li><li>• Keeps mops readily at hand when changing locations</li></ul>                                 |
| <b>100% autoclavable, electropolished stainless steel frame</b> | <ul style="list-style-type: none"><li>• Safe for autoclave at 121°C for 30 minutes</li><li>• Compatible with most cleanroom disinfectants and cleaners</li></ul>                                       |

## Product Features

### Stainless steel diffuser

A stainless steel disinfectant diffuser tray helps to evenly saturate every mop head. Simply pour the disinfectant straight into the diffuser and wait for 5 mins for full saturation.




### Stainless steel "A" frame

Each bucket has a stainless steel easy-fit mop applicator frame which coupled with the mop head design, means the mop heads can be fitted hands free.



### Hands-free mop head removal tool

The hands-free removal tool is suitable use with the magnetic QuickTask Flat Mop Head Frames, 2906 (stainless steel) and 2699P (polypropylene). It also includes a frame for holding a waste disposal bag. The waste bag holder can be used with sterile or nonsterile waste bags for complete hands free removal and disposal of dirty mop heads.



### Integral mop holders

Two mop holders with handle clasps on either side of the trolley allow for convenient mop storage during transport and storage.



Product Information

Dimensions

Mop Saturation System with polypropylene buckets (2941U2D)

Trolley 44.5 (L) x 49.0 (W) x 104cm (H)  
15L Bucket 15.3 (L) x 47.6 (W) x 25cm (H)

Mop Saturation System with stainless steel buckets (2940U2SD)

Trolley 44.5 (L) x 49.0 (W) x 104cm (H)  
10L Bucket 17.0 (L) x 49.0 (W) x 20cm H)



| Materials of construction         |                                                                 |
|-----------------------------------|-----------------------------------------------------------------|
| Trolley                           | Stainless steel, type 304                                       |
| Handle Clips                      | Stainless steel                                                 |
| Diffuser / A Frames/ Removal Tool | Stainless steel, type 304                                       |
| Castors                           | Stainless steel frames with blue Kryptonite autoclavable wheels |
| Finish                            | Electropolished                                                 |
| Buckets                           | Polpropylene copolymer or stainless steel, type 316, deep drawn |

For more information or to request a trial,  
email [infoeu@contecinc.com](mailto:infoeu@contecinc.com) or phone + 33 (0) 2 97 43 76 98.

## Ordering Information

| Part No  | Description                                                                                                                                                             | Quantity |
|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| 2941U2D  | Contec Hands-Free Mop Saturation System, two 15L polypropylene buckets, two x"A" frames, diffuser, utility handle with two 6L buckets and hands-free mop removal tool   | Each     |
| 2940U2SD | Contec Hands-Free Mop Saturation System, two 10L stainless steel buckets, two x"A" frames, diffuser, utility handle with two 6L buckets and hands-free mop removal tool | Each     |

### Hands Free Mop Head Frames

|       |                                                             |      |
|-------|-------------------------------------------------------------|------|
| 2906  | QuickTask Magnetic Mop Head Frame<br><i>Stainless steel</i> | Each |
| 2699P | QuickTask Magnetic Mop Head Frame<br><i>Polypropylene</i>   | Each |



QuickTask Magnetic  
Mop Head Frame 2906



QuickTask Magnetic Mop  
Head Frame 2699P

### Quick Connect Mop Handles

|       |                                                                                             |      |
|-------|---------------------------------------------------------------------------------------------|------|
| 2643  | QuickConnect Extendable Handle (130 - 230cm)<br><i>Anodised aluminium telescopic handle</i> | Each |
| 2645  | QuickConnect Extendable Handle (130 - 230cm)<br><i>Stainless steel telescopic handle</i>    | Each |
| 2725E | QuickConnect Extendable Handle (150cm)<br><i>Stainless steel one piece handle</i>           | Each |

### Accessories and spares

|          |                                                         |                              |
|----------|---------------------------------------------------------|------------------------------|
| BNBG0001 | Disposal bag for mop removal tool                       | 80 bags per case             |
| BNBG0002 | Irradiated disposal bag for mop removal tool            | 80 bags per case             |
| BKTBAG   | Bucket bag liners for 15L polypropylene buckets         | 2 per bag / 20 bags per case |
| BKTBAG2  | Sterile bucket bag liners for 15L polypropylene buckets | 3 per bag / 20 bags per case |
| PB6BS-3  | Polypropylene utility bucket 6L                         | 2 per case                   |
| UBKT0009 | 15L polypropylene buckets, red and grey (set of two)    | 1 set per case               |
| 2618     | 10L stainless steel buckets (set of two)                | 1 set per case               |
| 2951     | Stainless steel "A" frame                               | Each                         |
| 6203     | Diffuser for stainless steel buckets                    | Each                         |
| 6204     | Diffuser for polypropylene buckets                      | Each                         |

Copyright© 2022 Contec, Inc. All rights reserved. INT217 260422