

Contec Compact Bucket System 2.0

IMPROVED multiple bucket system for use with Contec's flat and curved mops

Contec's autoclavable Compact Bucket System is an all-in-one solution to make cleaning and disinfecting easier and more efficient. The trolley is designed for use with Contec mops such as the VertiKlean MAX, VertiKlean MAX Sealed Edge, EasyCurve and QuickTask Mopping Systems.

The stainless steel trolley is available in multiple configurations to meet the unique needs of your environment. It is available with either two or three, autoclavable polypropylene buckets, or with three stainless steel buckets, and a utility trolley handle. The utility handle allows two small buckets (6L) or one large bucket (15L) to be positioned on the handle providing additional storage for extra supplies such as clean mop heads, spray bottles, wipes, and other items as needed.

The trolley frame has a mop head removal tool on the front for easy removal of a VertiKlean MAX or MAX Sealed Edge mop head. An optional hands-free removal tool is also available for both the VertiKlean MAX mop heads and the QuickTask mop heads. Two, improved design, mop holders with handle hooks on either side of the trolley allow for convenient mop storage during transport and storage.

The systems are provided with stainless steel debris screens. The screen is positioned in the base of the clean and rinse buckets and prevents the mop from touching the bottom of the bucket where unwanted contaminants settle.



Features	Benefits
Compact polypropylene or stainless steel buckets with integral drip cap	- Keeps buckets in place while in use and prevents drips between the buckets and floor. - Buckets can hold a curved or flat wringer for curved or flat mops
Graduated polypropylene buckets in imperial and metric measurements available in 3 colours	- Different colours can be used to denote waste, rinse, and clean solution. - Dilution of concentrate is made easier.
Improved castors and connections	- Significantly reduces noise during use - More durable attachments with less "rattle"
Utility handle basket holds 2 x 6L buckets	Additional storage for clean mop heads, solution bottles, wipes, and other cleaning supplies if needed
Four rotating, lockable, quiet castors	- Excellent manoeuvrability; ideal for small cleanrooms & tight spaces - Trolley position can be secured during cleaning tasks
Improved on trolley storage for two mop handles and frames	- Allows convenient storage of two mop handles and frames keeping mops out of the way - Keeps mops readily at hand when changing locations
Integral mop head removal tool or optional hands-free mop head removal tool	- Allows easy hands-free removal of the VertiKlean MAX and QuickTask mop heads - Prevents cross-contamination during cleaning - Used mop heads can easily be discarded
100% autoclavable, electropolished stainless steel frame	- Safe for autoclave at 121°C for 30 minutes allowing it to be used in the most critical environments - Compatible with most cleanroom disinfectants and cleaners

Product Features


Integral mop head removal tool

Each size of trolley frame has an integral stainless steel mop head removal tool on the front for easy removal of a VertiKlean MAX or MAX Sealed Edge mop head.



Optional hands-free mop head removal tool: 6033 - improved

An optional hands-free removal tool is also available to use with the VertiKlean MAX and SE mop heads. The stainless steel tool is screwed onto mounting points on the back of the trolley to prevent rattle and includes a frame for holding disposal bags. The waste bag holder can be used with waste bags for complete hands free removal and disposal of dirty mop heads.



Optional hands-free mop head removal tool: 6034 - improved

An optional hands-free removal tool is also available to use with the range of QuickTask Mop Heads. The stainless steel tool is screwed onto mounting points on the back of the trolley to prevent rattle and includes a frame for holding disposal bags. The waste bag holder can be used with waste bags for complete hands free removal and disposal of dirty mop heads. In order to use this hands-free option, the QuickTask magnetic mop head frames must be used, 2906 (stainless steel) and 2699P (polypropylene).




Integral mop holders - improved

Two improved design mop holders with handle hooks on either side of the trolley allow for convenient mop storage during transport and storage. The new design prevents an empty mop head frame from sliding around when the trolley is being moved.



Integral debris screens

Each option of bucket system is provided with stainless steel debris screens. The screen is positioned in the base of the clean and rinse buckets and prevents the mop from touching the bottom of the bucket where unwanted contaminants settle.



"Quiet" castors - improved

The new castors provide a smoother ride on textured flooring creating one of the quietest cleanroom mopping trolleys on the market. Each castor locks and swivels independently for excellent manoeuvrability and so the trolley can be secured in position during cleaning.



Product Information	
Packaging Materials	Cases corrugated fibreboard (PAP) 
Materials of construction	- Trolley - Stainless steel, type 304 - Handle Clips - Stainless steel - Wringer and Removal Tools - Stainless steel, type 304 (sold separately) - Castors - Stainless steel frames with blue rubber autoclavable wheels - Finish - Electropolished - Mop Head Frames (2906) Stainless steel, type 304 and (2699P) Polypropylene - Buckets - Polypropylene copolymer/stainless steel, type 316, deep drawn - Disposal Bags - Low-density polyethylene (LDPE) 

Dimensions

Compact Double Bucket System
with Utility handle (2942U2B)



Trolley 63 (L) x 67 (W) x 104 (H) cm
Buckets 17 (L) x 51.5 (W) x 26 (H) cm
Utility Buckets 18 (L) x 23.5 (W) x 23.5 (H) cm

Compact Triple Bucket System
with Utility handle (2942U3B)



Trolley 81 (L) x 67 (W) x 104 (H) cm
Buckets 17 (L) x 51.5 (W) x 26 (H) cm
Utility Buckets 18 (L) x 23.5 (W) x 23.5 (H) cm

Compact Triple Bucket System
with Utility handle (2942U3S)



Trolley 81 (L) x 67 (W) x 104 (H) cm
Buckets 17.5 (L) x 48.5 (W) x 20 (H) cm

QuickTask Magnetic
Mop Head Frame 2906



QuickTask Magnetic
Mop Head Frame 2699P



QuickConnect Layflat
Mop Head Frame 2652LF



Ordering Information

Part no.	Description	Packaging
2942U2B	Compact Bucket System, two 15L polypropylene buckets with utility handle, two 6L buckets and one debris screen	Each
2942U3B	Compact Bucket System, three 15L polypropylene buckets with utility handle, two 6L buckets and two debris screens	Each
2942U3S	Compact Bucket System, three 10L stainless steel buckets with utility handle and two debris screens	Each

Wringers

2689	Stainless steel flat wringer for 15L polypropylene buckets	Each
2690	Stainless steel curved wringer for 15L polypropylene buckets	Each
2756	Stainless steel flat mop wringer for polypropylene and stainless steel systems	Each
6029	Stainless steel flat wringer for 10L stainless steel buckets	Each

Hands Free Mop Removal

6033	VertiKlean MAX Hands-free mop removal tool (includes frame to hold disposal bags)	Each
6034	QuickTask Hands-free mop removal tool (includes frame to hold disposal bags)	Each
BNBG0001	Disposal bag for mop removal tools	80 Bags/case
BNBG0002	Irradiated disposal bag for mop removal tools	80 Bags/case
2906	QuickTask Magnetic Mop Head Frame Stainless steel	Each
2699P	QuickTask Magnetic Mop Head Frame Polypropylene	Each

Accessories and spares

PB6BS-3	Polypropylene utility bucket 6L	2 per case
UBKT0008	Red, blue, grey 15L polypropylene buckets (set of three)	1 set per case
UBKT0009	Red and grey 15L polypropylene buckets (set of two)	1 set per case
2675	Debris screen for 15L polypropylene buckets	Each
6028	Debris screen for 10L stainless steel buckets	Each
BKTBAG	Bucket bag liners for 15L polypropylene buckets	2 per bag / 20 bags per case
BKTBAG2	Sterile bucket bag liners for 15L polypropylene buckets	3 per bag / 20 bags per case

The previous versions of the Compact Bucket System are still supported in terms of spares, accessories and replacement parts, please get in touch for details.

For more information or to request a trial or sample, email infoeu@contecinc.com or phone + 33 (0) 2 97 43 76 98.

Copyright© 2024 Contec, Inc. All rights reserved. INT146 210324