

CONSTIX® Sealed Foam Swab

SF-12

Small sealed foam swab

CONSTIX® SF-12 sealed foam swab consists of polyurethane foam bonded to a polypropylene handle without the use of adhesives or binders.


The polyurethane open-cell foam head provides good particle entrapment and removal. The absorbent foam enables solvents, such as isopropanol and ethanol, to be readily absorbed for applications involving solvent delivery or removal. SF-12 swab is excellent for applying resins and adhesives.

Though compatible with many common solvents, the SF-12 is not recommended for use with ketones such as acetone or MEK.



Features	Benefits
Small head size	Enables good access to small features and difficult to reach surfaces
Absorbent polyurethane foam tip	Ideal for solvent delivery or removal

Part No.	Description	Size	Packaging
SF-12	CONSTIX Sealed foam swab	Head dimension: 0.16" x 0.40" (4.1 x 10.1 mm) Handle diameter: 0.10" (2.5 mm) Total length: 2.8" (71.1 mm)	500/case



Product Information	
Head material	100 PPI open-cell polyurethane foam
Handle material	100% polypropylene
Construction	Thermally sealed and attached
Packaging materials	- Outer bags (OB1, OB2): low density polyethylene (LDPE)  - Case (CS): corrugated fiberboard (PAP) 
Environment	ISO 5-8 Grade C/D

Recycle Symbols				
PET	HDPE	LDPE	PP	PAP
				

Packaging	EA/OB1	OB1/OB2	OB2/CS	EA/CS
SF-12	500	1	1	500

EA = each; OB = outer bag; CS = case