

European Headquarters

Tiger-Vac Europa S.R.L.
Via Marie Curie 17
Zona Industriale Ponte Rizzoli
Ozzano Emilia, BO 40064

Tel: ((39) 051 79.53.52)
Fax: ((39) 051 4695077)
Website: <http://www.tiger-vac.eu>
Email: info@tiger-vac.it

International Headquarters

Tiger-Vac International Inc.
2020 Dagenais Blvd. Ouest
Laval, Quebec
Canada H7L 5W2

Tel: ((39) 051 79.53.52)
Fax: ((39) 051 4695077)
Website: <http://www.tiger-vac.com>
Email: sales@tiger-vac.com




HEPA - inclus



Haute efficacité



Charbons actifs



Protection des interférences électromagnétiques



Récupération du mercure



Porter des vêtements de protection

Spécifications for MRV-8 POLY

Name	Part Number	Tension	Fréquence	Phase	Puissance électrique	Puissance	Ampérage	Flux d'air	Dépression	Type de la prise d'alimentation	Récup. des poussières - Cuve
MRV-8 POLY	110116B	240 V	50 Hz	Single	1000 W	1 kW	4.6 amps.	204 m³/h	2410 mm H ₂ O	European	15.1 L
	Dimensions: H66 cm x W46 cm x L46 cm Weight: 20 kg. Sound Level: 70 dB(A)										
MRV-8 POLY	110116C	240 V	50 Hz	Single	1000 W	1 kW	4.6 amps.	204 m³/h	2410 mm H ₂ O	UK	15.1 L
	Dimensions: H66 cm x W46 cm x L46 cm Weight: 20 kg. Sound Level: 70 dB(A)										
MRV-8 POLY	110116D	240 V	50 Hz	Single	1000 W	1 kW	4.6 amps.	204 m³/h	2410 mm H ₂ O	Swiss	15.1 L
	Dimensions: H66 cm x W46 cm x L46 cm Weight: 20 kg. Sound Level: 70 dB(A)										
MRV-8 POLY	110116E	240 V	50 Hz	Single	1000 W	1 kW	4.6 amps.	204 m³/h	2410 mm H ₂ O	Chinese	15.1 L
	Dimensions: H66 cm x W46 cm x L46 cm Weight: 20 kg. Sound Level: 70 dB(A)										

Veuillez noter que les spécifications peuvent être modifiées sans préavis

Feuille technique for MRV-8 POLY

FILTERS AND ACCESSORIES - Included

Numero de la pièce	Description
213677	POLYESTER FILTER ASSEMBLY WITH CLAMP, FOR MRV-8 CARBON HOUSING

ACTIVATED CARBON CARTRIDGE - Included

Numero de la pièce	Description
212200A	CARBON HOUSING ASSEMBLY WITH 1.5mm MERSORB & WITH HEPA FILTER INSTALLED

MERCURY RECOVERY SEPARATOR AND ACCESSORIES - Included

Numero de la pièce	Description
212208	MERCURY SEPARATOR -STAINLESS STEEL(INCLUDES 2 MERCURY RECOVERY JARS AND (2) LIDS FOR JAR)
212211	CLEAR SUCTION HOSE ASSEMBLY 1"(25.4mm)x8'(2.4m) FOR USE WITH MERCURY SEPARATOR

JAR FOR MERCURY RECOVERY - Optional

Numero de la pièce	Description
212210	JAR FOR MERCURY RECOVERY 20oz(540 ml) WITH LID

HOURLY COUNTER - Included

Numero de la pièce	Description
213058	HOUR COUNTER 100 V TO 230V, FOR MRV MODELS



2, rue André Citroën 95130 FRANCONVILLE - Site : www.sterigene.com
Tél. : +33 (0)1 34 44 23 23 - Fax : +33 (0)1 34 44 23 24 - e-mail : sterigene@sterigene.com